



SU212

Bell 12V

Technical Features

Electric current

Rated current	0.33 A
---------------	--------

Dimensions

Dimensions	80 x 18 mm
Height	80 mm
Width	18 mm
Depth	65 mm

Use conditions

Operating temperature	-10 - 40 °C
Storage/transport temperature	-25 - 60 °C

Connection

Cross-section flexible conductor	4 mm ²
Cross-section rigid conductor	6 mm ²

Power

Total power loss under IN	5 W
Power consumption VA	5 VA

Equipment

Noise level	85
-------------	----

Frequency

Frequency	0 - 50 Hz
-----------	-----------

Capacity

Number of modules	1
-------------------	---

Voltage

Rated operational voltage U _e	8 - 12 V
--	----------

Illustrations | Drawings

