



SU212

**Bell 12V**

**Technical Features**

**Electric current**

Rated current	0.33 A
---------------	--------

**Dimensions**

Dimensions	80 x 18 mm
Height	80 mm
Width	18 mm
Depth	65 mm

**Use conditions**

Operating temperature	-10 - 40 °C
Storage/transport temperature	-25 - 60 °C

**Connection**

Cross-section flexible conductor	4 mm <sup>2</sup>
Cross-section rigid conductor	6 mm <sup>2</sup>

**Power**

Total power loss under IN	5 W
Power consumption VA	5 VA

**Equipment**

Noise level	85
-------------	----

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Capacity**

Number of modules	1
-------------------	---

**Voltage**

Rated operational voltage Ue	8 - 12 V
------------------------------	----------

**Illustrations | Drawings**

