



VT12S

12M 1Row DIN Surface Metal BOX, No Door

Technical Features

Voltage

Nominal voltage	230 - 415 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Equipment

Number of rails	1
Number of rows	1

Capacity

Number of modules	12
-------------------	----

Dimensions

Height	259 mm
Width	309 mm
Depth	71 mm
Built-in depth	70 mm

Cover, door

Number of locks	0
-----------------	---

Dimensions

Number of width units	12
-----------------------	----

Cover, door

Door/cover is transparent	No
---------------------------	----

Connection

Number of conduit inlets	16
--------------------------	----

Connectivity

Mounting type	Screw mounting
---------------	----------------

Materials

Material	Steel
RAL code	9002
Colour	Grey white

Safety

Protection class	Isolation class I
Impact resistance IK	IK05

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes