



75142830



**KNX glass sensor 2gang comf, intg bus coupl. unit, KNX-TS sensor, glass p.white**

**Technical Features**

**Installation, mounting**

Mounting on Flush mounting

**Use conditions**

Operating temperature -5 - 45 °C

**Functions**

With room temperature controller Yes

**Power**

Current consumption 12.50 mA

**Dimensions**

Built-in depth 24.20 mm

Built-in depth flush-mounted boxes 27 mm

Height 160 mm

Width 86 mm

Depth 37.70 mm

**Equipment**

Number of actuation points 4

**Controls and indicators**

With LED indication Yes

**Materials**

Colour Polar white

RAL code 9010

Material Glass

Surface finish Glossy  
Matt

**Accessories**

Has labelling field No

**Screen**

With display No

**Texts**

Function For switch, push-button, dimmer and shutter functions  
Blocking function for sensor surface e.g. for cleaning the glass surface

Installation mode For vertical mounting

Temperature Additional connection for external temperature sensor  
Integrated temperature sensor for operation as controller extension unit  
Temperature measurement via internal Temperature sensor or external communication object

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes