



VS418PZD

Small distributor,golf,surface,MM,4row,72M,white door, slotted

**Technical Features**

**Installation, mounting**

|                            |                  |
|----------------------------|------------------|
| Suitable for outdoor usage | No               |
| Mounting on                | Surface mounting |

**Equipment**

|                            |    |
|----------------------------|----|
| Number of rails            | 4  |
| Number of rows             | 4  |
| With lock                  | No |
| Has neutral terminal block | No |

**Capacity**

|                   |    |
|-------------------|----|
| Number of modules | 72 |
|-------------------|----|

**Functions**

|                     |     |
|---------------------|-----|
| With conduit inlets | Yes |
|---------------------|-----|

**Dimensions**

|        |        |
|--------|--------|
| Height | 647 mm |
| Width  | 390 mm |
| Depth  | 99 mm  |

**Cover, door**

|                         |   |
|-------------------------|---|
| Number of cabinet doors | 1 |
| Number of locks         | 0 |

**Dimensions**

|                       |    |
|-----------------------|----|
| Number of width units | 18 |
|-----------------------|----|

**Cover, door**

|                           |    |
|---------------------------|----|
| Door/cover is transparent | No |
|---------------------------|----|

**Materials**

|          |            |
|----------|------------|
| Material | Plastic    |
| RAL code | 9010       |
| Colour   | Pure white |

**Equipment**

|                             |     |
|-----------------------------|-----|
| Has earthing terminal block | No  |
| Has mounting plate          | Yes |

**Safety**

|                      |                              |
|----------------------|------------------------------|
| Impact resistance IK | IK07                         |
| Locking type         | Snap on lock<br>Without lock |
| Glow wire test       | 650 °C                       |

**Sustainability**

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|