

Product Datasheet

LNH0125M



LNH0125M

HRC LV fuse NH00 gG AC500V 125A double indicator with live gripping-lugs

Technical Features

Architecture

Curve	gG
-------	----

Fuse

Fuse size	NH00
Fuse characteristics	gG

Voltage

Type voltage supply	AC/DC
Rated operational voltage Ue	500 - 500 V
Rated voltage at AC 50 Hz	500 - 500 V

Electric current

Rated current	125 A
---------------	-------

Use conditions

Insulated	No
-----------	----

Main electrical attributes

Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	120 kA
---	--------

Power

Total power loss under IN	10 W
---------------------------	------

Dimensions

Height	58.50 mm
Width	21 mm
Depth	79 mm

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes