



KB181G1

Insulated prong busbar 1P 80A 16mm² 6C for RCBO

Technical Features

Electric current

Rated current 80 A

Architecture

Number of poles 1

Dimensions

Length 184 mm

Voltage

Rated impulse withstand voltage Uimp 4000 V

Rated operational voltage Ue 415 - 415 V

Connection

Cross-section rigid conductor 16 mm²

Connector/plug type Phase busbar with pin

Capacity

Number of modules 11

Sustainability

REACH-SVHC free Yes

RoHS conform Yes