




47403512



SCHUKO soc. out. hinged cover surface-mtd, W.1, p. white, matt, plastic

Technical Features

Electric current

Rated current	16 A
---------------	------

Voltage

Rated voltage	250 V
---------------	-------

Nominal voltage	250 - 250 V
-----------------	-------------

Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	Polar white
--------	-------------

RAL code	9010
----------	------

Surface finish	Matt
----------------	------

Material	Thermoplastic
----------	---------------

Treatment	Untreated
-----------	-----------

Dimensions

Height	76 mm
--------	-------

Width	76 mm
-------	-------

Depth	63 mm
-------	-------

Number of units	1
-----------------	---

Built-in depth flush-mounted boxes	0 mm
------------------------------------	------

Connection

Conductor cross-section	1.0 - 2.5 mm²
-------------------------	---------------

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Connectivity

Type of connection	Plug-in connection
--------------------	--------------------

Mounting type	Screw mounting Claw mounting
---------------	---------------------------------

Equipment

Connector/plug type socket outlet	SCHUKO
-----------------------------------	--------

Rotated central insert	No
------------------------	----

With hinged lid	Yes
-----------------	-----

With round protective earth pin	No
---------------------------------	----

With signal lamp	No
------------------	----

With lock	No
-----------	----

Accessories

Has labelling field	No
---------------------	----

Cover, door

Type of lid	Self-closing hinged cover, can be arrested in end position
-------------	--

Capacity

Number of modules	1
-------------------	---

Safety

With enhanced contact protection	No
----------------------------------	----

Impact resistance IK	IK05
----------------------	------

Ingress Protection (IP) class	IP55
-------------------------------	------

Functions		
With orientation lighting		No
With function lighting		No
Texts		
Imprint		Without imprint
Cover		Complete housing
Protection		Without enhanced contact protection
Type of connection		With plug-in terminals
Terminal		With Wago clip-in 2-wire connection terminal for wiring
	With two clip-in places for Wago 2-wire connection terminals in the housing floor	
Sustainability		
Halogen free		Yes
RoHS conform		Yes