



JN204BG

**250A 16 Way 125A Outgoers Glazed**

**Technical Features**

**Installation, mounting**

Suitable for outdoor usage	No
Mounting on	Surface mounting

**Electric current**

Rated current	250 A
---------------	-------

**Equipment**

With lock	No
Has neutral terminal block	Yes

**Dimensions**

Height	1550 mm
Width	710 mm
Depth	178.40 mm

**Cover, door**

Number of cabinet doors	1
Door/cover is transparent	Yes

**Materials**

Material	Steel
RAL code	7035 9001
Colour	Light grey

**Equipment**

Has earthing terminal block	Yes
-----------------------------	-----

**Safety**

Protection class	Isolation class III
Impact resistance IK	IK05
Ingress Protection (IP) class	IP30
Locking type	Key lock Quarter turn lock

**Sustainability**

RoHS conform	Yes
--------------	-----