



75142935



**KNX glass sensor 2gang comf, intg bus coupling unit, KNX-TS sensor, glass black**

**Technical Features**

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Use conditions**

Operating temperature	-5 - 45 °C
-----------------------	------------

**Functions**

With room temperature controller	Yes
----------------------------------	-----

**Power**

Current consumption	12.50 mA
---------------------	----------

**Dimensions**

Built-in depth	24.20 mm
Built-in depth flush-mounted boxes	27 mm
Height	160 mm
Width	86 mm
Depth	37.70 mm

**Equipment**

Number of actuation points	4
----------------------------	---

**Controls and indicators**

With LED indication	Yes
---------------------	-----

**Materials**

Colour	Black
RAL code	9005
Material	Glass
Surface finish	Glossy Matt

**Accessories**

Has labelling field	No
---------------------	----

**Screen**

With display	No
--------------	----

**Texts**

Function	For switch, push-button, dimmer and shutter functions Blocking function for sensor surface e.g. for cleaning the glass surface
Installation mode	For vertical mounting
Temperature	Additional connection for external temperature sensor Integrated temperature sensor for operation as controller extension unit Temperature measurement via internal Temperature sensor or external communication object

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes