



75142930



KNX glass sensor 2gang comf, intg bus coupl. unit, KNX-TS sensor, glass p.white

Technical Features

Installation, mounting

Mounting on Flush mounting

Use conditions

Operating temperature -5 - 45 °C

Functions

With room temperature controller Yes

Power

Current consumption 12.50 mA

Dimensions

Built-in depth 24.20 mm
 Built-in depth flush-mounted boxes 27 mm
 Height 160 mm
 Width 86 mm
 Depth 37.70 mm

Equipment

Number of actuation points 4

Controls and indicators

With LED indication Yes

Materials

Colour Polar white
 RAL code 9010
 Material Glass
 Surface finish Glossy
 Matt

Accessories

Has labelling field No

Screen

With display No

Texts

Function For switch, push-button, dimmer and shutter functions
 Blocking function for sensor surface e.g. for cleaning the glass surface
 Installation mode For vertical mounting
 Temperature Additional connection for external temperature sensor
 Integrated temperature sensor for operation as controller extension
 unit
 Temperature measurement via internal Temperature sensor or external
 communication object

Sustainability

REACH-SVHC free Yes
 RoHS conform Yes