



EG493E



Yearly time switch 4 channels, digital, 4 modules

Technical Features

Frequency

Frequency	50 - 60 Hz
-----------	------------

Power

230 V incandescent and halogen lamp	1500 W
-------------------------------------	--------

Functions

Power reserve in years	5 y
With network synchronisation	No
With quartz synchronisation	Yes
Number of function channels	4

Equipment

Accuracy per day	0.20 s
With impulse programme	Yes
Number of channels	4

Settings

Daily programme	No
Weekly programme	No
Annual programme	Yes

Use conditions

Operating temperature	-10 - 50 °C
-----------------------	-------------

Connection

Cross-section flexible conductor	0.75 - 2.5 mm ²
Cross-section rigid conductor	0.75 - 2.5 mm ²

Texts

Type of connection	With quickconnect plug-in terminals
Function	With pulse function Keylock via PIN Presence simulation With operating hours meter

Dimensions

Height	90 mm
Width	70 mm
Depth	65 mm

Main electrical attributes

Minimum interval between 2 switching times	1 min
--	-------

Capacity

Number of modules	4
-------------------	---

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes