




EKSQ405BL

height adjustable cassette stainl. steel sq. 405mm blind ht. i/e 28/44mm, 20kN

Technical Features

Architecture

With opening carpeting	Yes
------------------------	-----

Shape

Shape	Square
-------	--------

Dimensions

Built-in depth	116 mm
Built-in length	405 mm
Built-in width	405 mm
Height	116 mm
Nominal size	244 mm

Configuration

Installation size (underfloor installations)	Q12
--	-----

Dimensions

Thickness of carpet recess	28 mm
----------------------------	-------

Use conditions

Vertical load applied across large surface area (heavy load)	20 kN
Vertical load applied across small surface area	3 kN

Equipment

Number of outlet boxes	0
Number of conduit outlets	0

Installation, mounting

Suitable for recessed floor mounting	Yes
Suitable for raised floor installation	Yes

Materials

Material	Stainless steel
Colour	Stainless steel

Installation, mounting

Suitable for sub-floor duct	Yes
-----------------------------	-----

Safety

Impact resistance IK	IK10
Ingress Protection (IP) class	IP20

Sustainability

Halogen free	Yes
RoHS conform	Yes