



WGDS213S

### 13A TWIN SWITCHED SOCKET

#### Technical Features

##### Voltage

Rated voltage 250 V

##### Electric current

Rated current 13 A

##### Frequency

Frequency 50 - 60 Hz

##### Materials

Colour White

Surface finish Glossy

Material Polycarbonate (PC)

##### Dimensions

Height 86 mm

Width 146 mm

Depth 28 mm

##### Equipment

Rotated central insert No

With hinged lid No

##### Safety

Ingress Protection (IP) class IP20

##### Suitable for

shark

##### Sustainability

Halogen free Yes

REACH-SVHC free Yes

RoHS conform Yes