




EKSQ405TM

height adjustable cassette stainl. steel sq. 405mm TM ht. i/e 28/44mm, 20kN

Technical Features

Shape

Shape	Square
-------	--------

Dimensions

Built-in depth	116 mm
Built-in length	405 mm
Built-in width	405 mm
Height	116 mm
Nominal size	244 mm

Configuration

Installation size (underfloor installations)	Q12
--	-----

Dimensions

Thickness of carpet recess	28 mm
----------------------------	-------

Equipment

Chassis part for device cups	Yes
------------------------------	-----

Use conditions

Vertical load applied across large surface area (heavy load)	20 kN
Vertical load applied across small surface area	3 kN

Equipment

Number of built-in devices	12
Number of outlet boxes	3
Number of conduit outlets	1
Type of conduit outlet	Screwable

Installation, mounting

Suitable for recessed floor mounting	Yes
Suitable for raised floor installation	Yes

Materials

Colour conduit outlet	Silver
Material	Stainless steel
Colour	Stainless steel

Installation, mounting

Suitable for sub-floor duct	Yes
-----------------------------	-----

Safety

Impact resistance IK	IK10
----------------------	------

Sustainability

Halogen free	Yes
RoHS conform	Yes