


Product Datasheet

ATA205088014



ATA205088014

T piece for ATHEA trunking 20x50mm in brown

Technical Features

Dimensions

| | |
|--------|-------|
| Height | 20 mm |
| Width | 50 mm |

Accessories

| | |
|-------------------|---------|
| Type of accessory | Moulded |
|-------------------|---------|

Standards

| | |
|---|----|
| Suitable for functional integrity according to DIN4102-12 | No |
|---|----|

Materials

| | |
|-----------|---------------------------------------|
| Material | Acrylonitrile-Butadiene-Styrene (ABS) |
| Treatment | Untreated |
| Colour | Brown |
| RAL code | 8014 |

Safety

| | |
|-------------------------------|------|
| Impact resistance IK | IK07 |
| Ingress Protection (IP) class | IP40 |

Use conditions

| | |
|-----------------------|------------|
| Operating temperature | -5 - 60 °C |
|-----------------------|------------|

Equipment

| | |
|----------------------|----|
| With protective film | No |
|----------------------|----|

Suitable for

| | |
|-----------|--|
| ATA 20x50 | |
|-----------|--|

Sustainability

| | |
|-----------------|-----|
| Halogen free | Yes |
| REACH-SVHC free | Yes |
| RoHS conform | Yes |