



303303

On/off switch 3pole 16A/400V

Technical Features

Electric current

Switching current	16 A
-------------------	------

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Voltage

Rated voltage	400 V
---------------	-------

Materials

Material	Metal Plastic
----------	------------------

Identification

Assembly arrangement	Basic element
----------------------	---------------

Connectivity

Mounting type	Claw mounting
---------------	---------------

Controls and indicators

Number of buttons	1
-------------------	---

Dimensions

Dimensions	71 x 71 mm
Built-in depth	31 mm
Built-in depth flush-mounted boxes	35 mm

Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK07

Architecture

Control/operation element	Single rocker
---------------------------	---------------

Electric current

Rated current	16 A
---------------	------

Texts

Installation mode	With spreader claws
Type of connection	With screw terminals
Lighting	For lighting and monitoring circuit
Switch mode	3-pole off With predefined neutral position

Sustainability

RoHS conform	Yes
--------------	-----