



WGCT2RJRJ6

RJ11 + RJ45 cat6 outlet

Technical Features

Frequency	
Transmission bandwidth	0-250 MHz

Equipment	
With transparent label holder	No
Number of outputs	2

Use conditions	
Operating temperature	-20 - 45 °C

Equipment	
With hinged lid	No

Materials	
Colour	White

Connection	
Connector/plug type	RJ45

Materials	
Material	Polycarbonate (PC)

Safety	
Ingress Protection (IP) class	IP20

Voltage	
Rated voltage	0 V

Electric current	
Rated current	0 A

Dimensions	
Built-in depth	27 mm

Texts	
Outlet	With straight outlet
Protection	With dust protection sliders
Supporting plate/supporting ring	With supporting plate

Sustainability	
RoHS conform	Yes