



VM_SIZE_7

Consumer unit, Design30, 18way, twin tariff, config, 2*100A sw

Technical Features

Installation, mounting

Mounting on Surface mounting

Architecture

Number of poles 2

Functions

Has protection main switch Yes

Overvoltage protection Yes

Installation, mounting

Suitable for outdoor usage No

Capacity

Number of modules 18

Electric current

Rated current 100 A

Dimensions

Depth 102.50 mm

Height 240 mm

Width 471 mm

Thickness of sidewall 1 mm

Cover, door

Interlockable Yes

Door/cover is transparent No

Materials

RAL code 9010

Colour Pure white

Material Steel

Connection

Number of accessible phases 1

Scope of delivery

Number of earth leakage circuit breaker type A 2

Number of RCCB in enclosure 2

Equipment

Number of rows 1

Number of rails 1

Extension possible No

With socket outlet No

Safety

Impact resistance IK IK05

Ingress Protection (IP) class IP2XC

Sustainability

RoHS conform Yes