

Product Datasheet

WBMD400UPB



WBMD400UPB

Mechanism, dimmer, universal push button

Technical Features

Frequency	
Frequency	50 - 50 Hz

Materials	
Colour	White
Material	Polycarbonate (PC)

Dimensions	
Height	24 mm
Width	24 mm
Depth	51 mm

Architecture	
Control/operation element	Single push button

Power	
Power consumption standby	0.10 W

Lighting	
Dimmable 230 V LED lamp	3 - 70 W

Use conditions	
Operating temperature	-5 - 45 °C

Texts	
Dimming principle	Automatic setting of load-dependent switching principle (autodetect process) Phase cut-on or cut-off according to load type, self-learning
Fuse	Short-circuit and overload-proof (electronic fuse)
Installation mode	RotoLoc®
Type of connection	With screw terminals
Extension unit input	With extension unit input for slave push-button WBMESL
Operation and control	No Bluetooth interface