



HXA026H

Alarm contact low level 1NO+1NC 125V AC (x160-P160-x250-P250-x630-P630)

Technical Features

Electric current

Rated current	0.10 A
Rated current 230 V AC15	0.10 A

Connectivity

Type of connection	quickconnect
Mounting type	Click mounting

Connection

Type of contacts	1NC+1NO
Cross-section flexible conductor	0.5 - 1.25 mm ²
Cross-section rigid conductor	0.5 - 1.25 mm ²

Voltage

Rated impulse withstand voltage Uimp	1500 V
Type voltage supply	AC/DC

Power

Total power loss under IN	3 W
---------------------------	-----

Equipment

Number of INV contacts	0
Number of NC contacts	1

Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------