



JN4E01S

#### Technical Features

##### Dimensions

Height	304 mm
Width	690 mm
Depth	205 mm
Thickness of sidewall	1.50 mm

##### Safety

Ingress Protection (IP) class	IP41
Protection class	Isolation class I
Locking type	Screwed
Impact resistance IK	IK05

##### Equipment

Number of flange plate openings	2
---------------------------------	---

##### Installation, mounting

Mounting on	Surface mounting
Suitable for outdoor usage	No

##### Materials

Colour	Grey white
RAL code	9002
Treatment	Varnished
Material	Steel
Surface finish	Matt

##### Cover, door

Number of locks	0
Door/cover is transparent	No

##### Voltage

Nominal voltage	415 - 415 V
-----------------	-------------

##### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes