


Product Datasheet

385620



385620



Key push-button for profile half cylinders splash-protected flush-mounted IP44

Technical Features

Electric current

Switching current	10 A
Momentary contact current	10 A

Voltage

Rated voltage	250 V
---------------	-------

Architecture

Control/operation element	Key
---------------------------	-----

Materials

Material	Metal Plastic
Treatment	Untreated
Transparent	No

Dimensions

Height	71 mm
Width	71 mm
Depth	42 mm
Built-in depth	31.30 mm
Built-in depth flush-mounted boxes	35 mm

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Controls and indicators

Number of buttons	0
With feedback signal contact	No

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Safety

Ingress Protection (IP) class	IP44
Impact resistance IK	IK07

Texts

Imprint	Without imprint
Installation mode	For screw fastening Without spreader claws
Switch mode	Change-over contact, usable as NC or NO
Type of connection	With screw terminals

Suitable for

K.x / Q.x / R.x / S.x/B.x

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes