



FL209B

Polyester enclosure, Orion.Plus, plain door 500x300x200 mm

Technical Features

Cover, door

Door/cover is transparent	No
Number of cabinet doors	1
Number of locks	2

Dimensions

Depth	200 mm
Height	500 mm
Thickness of sidewall	2 mm
Width	300 mm

Electric current

Rated current	125 A
---------------	-------

Equipment

Number of flange plate openings	0
Number of rows	3

Installation, mounting

Mounting on	Surface mounting
Suitable for outdoor usage	Yes

Materials

Colour	Light grey
Material	Glass reinforced polyester
RAL code	7035
Treatment	Untreated

Safety

Impact resistance IK	IK10
Ingress Protection (IP) class	IP66
Locking type	3-Side 7 mm Key lock
Protection class	Isolation class II

Sustainability

RoHS conform	Yes
--------------	-----