



WGCL111B

10A 1G bell switch mark bell symbol

Technical Features

Electric current

Switching current 10 A

Voltage

Rated voltage 250 V

Architecture

Control/operation element Single rocker

Materials

Colour White

Surface finish Glossy

Material Polycarbonate (PC)

Treatment Untreated

Transparent No

Dimensions

Height 86 mm

Width 86 mm

Depth 25 mm

Built-in depth flush-mounted boxes 35 mm

Installation, mounting

Mounting on Flush mounting

Controls and indicators

Number of buttons 1

With feedback signal contact No

Connectivity

Type of connection Screw terminal

Safety

Ingress Protection (IP) class IP20

Accessories

Has labelling field No

Texts

Imprint With imprinted symbol bell

Suitable for

shark

Sustainability

RoHS conform Yes