



LNH1100M

HRC LV fuse NH1C gG AC500V 100A double indicator with live gripping-lugs

Technical Features

Architecture

Curve	gG
-------	----

Fuse

Fuse size	NH1C
Fuse characteristics	gG

Voltage

Type voltage supply	AC
Rated operational voltage Ue	500 - 500 V
Rated voltage at AC 50 Hz	500 - 500 V

Electric current

Rated current	100 A
---------------	-------

Use conditions

Insulated	No
-----------	----

Main electrical attributes

Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	120 kA
---	--------

Power

Total power loss under IN	9.40 W
---------------------------	--------

Dimensions

Height	64.50 mm
Width	135 mm
Depth	135 mm

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes