

Product Datasheet

WGDL111NP-12VNB



WGDL111NP-12VNB

12V 1G press switch with led;nb

Technical Features

Electric current

Switching current	10 A
-------------------	------

Voltage

Rated voltage	250 V
---------------	-------

Frequency

Frequency	50-60 Hz
-----------	----------

Architecture

Control/operation element	Single rocker
Number of poles	1

Power

Fluorescent lamps in duo circuit	0 W
----------------------------------	-----

Materials

Colour	Bronze
Surface finish	Matt
Material	Polycarbonate (PC)
Treatment	Varnished
Transparent	No

Dimensions

Height	22 mm
Width	90 mm
Depth	25 mm
Built-in depth	25 mm

Installation, mounting

Mounting on	Wall mounting
-------------	---------------

Controls and indicators

Number of buttons	1
-------------------	---

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK02

Texts

Switch mode	1-way
-------------	-------

Suitable for

shark	
-------	--

Sustainability

RoHS conform	Yes
--------------	-----