



WGDL111NP-12VNB

12V 1G press switch with led;nb

Technical Features

Electric current

Switching current 10 A

Voltage

Rated voltage 250 V

Frequency

Frequency 50 - 60 Hz

Architecture

Control/operation element Single rocker

Number of poles 1

Power

Fluorescent lamps in duo circuit 0 W

Materials

Colour Bronze

Surface finish Matt

Material Polycarbonate (PC)

Treatment Varnished

Transparent No

Dimensions

Height 22 mm

Width 90 mm

Depth 25 mm

Built-in depth 25 mm

Installation, mounting

Mounting on Wall mounting

Controls and indicators

Number of buttons 1

Connectivity

Type of connection Screw terminal

Connection

Connector/plug type British Standard

Safety

Ingress Protection (IP) class IP20

Impact resistance IK IK02

Accessories

Has labelling field No

Texts

Switch mode 1-way

Suitable for

shark

Sustainability

RoHS conform Yes