



BD163T

**Earth leakage add-on-block 3P 63A 100mA A Class 1mod**

**Technical Features**

**Voltage**

Rated operational voltage $U_e$	240 - 415 V
Rated insulation voltage $U_i$	500 V
Rated impulse withstand voltage $U_{imp}$	4000 V

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Electric current**

Rated residual operating current $I_{dn}$	100 mA
Rated current	63 A

**Architecture**

Number of poles	3
Neutral position	Right

**Capacity**

Number of modules	1
-------------------	---

**Connectivity**

Type of connection	Screw terminal
--------------------	----------------

**Dimensions**

Height	121 mm
Width	70.80 mm
Depth	69.10 mm

**Sustainability**

RoHS conform	Yes
--------------	-----