

Product Datasheet

BE163T



BD163T

Earth leakage add-on-block 3P 63A 100mA A Class 1mod

Technical Features

Voltage

Rated operational voltage Ue	240 - 415 V
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	4000 V

Frequency

Frequency	50 - 50 Hz
-----------	------------

Electric current

Rated residual operating current Idn	100 mA
Rated current	63 A

Architecture

Number of poles	3
Neutral position	Right

Capacity

Number of modules	1
-------------------	---

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Dimensions

Height	121 mm
Width	70.80 mm
Depth	69.10 mm

Sustainability

RoHS conform	Yes
--------------	-----