



11372089

Centre plate f. rot. dimmer/rot. potentiometer, setting knob, R.1/R.3, p.wh.gl.

Technical Features

Architecture

| | |
|---------------------------|------------------------|
| Control/operation element | Push & rotative switch |
|---------------------------|------------------------|

Materials

| | |
|----------------|---------------|
| Colour | Polar white |
| RAL code | 9010 |
| Surface finish | Glossy |
| Material | Thermoplastic |
| Treatment | Untreated |

Dimensions

| | |
|---------------|----------|
| Height | 58.10 mm |
| Width | 58.10 mm |
| Depth | 10 mm |
| Diameter axis | 4 mm |

Connectivity

| | |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

Equipment

| | |
|--------------------------------|----|
| Monitoring window/light outlet | No |
|--------------------------------|----|

Accessories

| | |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

Safety

| | |
|-------------------------------|--------------------------------------|
| Ingress Protection (IP) class | IP20 |
| Usable in higher IP class | IP44 in combination with sealing set |

Texts

| | |
|-------------------|------------------------------|
| Imprint | Centre plate without imprint |
| Installation mode | For screw fastening |

Suitable for

| | |
|-----|--|
| R.x | |
|-----|--|

Sustainability

| | |
|-----------------|-----|
| Halogen free | Yes |
| REACH-SVHC free | Yes |
| RoHS conform | Yes |