



11372089

Centre plate f. rot. dimmer/rot. potentiometer, setting knob, R.1/R.3, p.wh.gl.

#### Technical Features

##### Architecture

Control/operation element	Push & rotative switch
---------------------------	------------------------

##### Materials

Colour	Polar white
RAL code	9010
Surface finish	Glossy
Material	Thermoplastic
Treatment	Untreated

##### Dimensions

Height	58.10 mm
Width	58.10 mm
Depth	10 mm
Diameter axis	4 mm

##### Connectivity

Mounting type	Screw mounting
---------------	----------------

##### Equipment

Monitoring window/light outlet	No
--------------------------------	----

##### Accessories

Has labelling field	No
---------------------	----

##### Safety

Ingress Protection (IP) class	IP20
Usable in higher IP class	IP44 in combination with sealing set

##### Texts

Imprint	Centre plate without imprint
Installation mode	For screw fastening

##### Suitable for

R.x	
-----	--

##### Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes