



11372079

Centre plate for speed cont., setting knob, R.1/R.3, p. white glossy

Technical Features

Architecture

Control/operation element	Rotative
---------------------------	----------

Materials

Colour	Polar white
RAL code	9010
Surface finish	Glossy
Material	Thermoplastic
Treatment	Untreated

Dimensions

Height	58.30 mm
Width	58.30 mm
Depth	18.90 mm
Diameter axis	4 mm

Connectivity

Mounting type	Screw mounting
---------------	----------------

Equipment

Monitoring window/light outlet	No
--------------------------------	----

Accessories

Has labelling field	No
---------------------	----

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Texts

Imprint	With imprinted symbol curve
Installation mode	For screw fastening

Suitable for

R.x	
-----	--

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes