



11372079

**Centre plate for speed cont., setting knob, R.1/R.3, p. white glossy**

**Technical Features**

**Architecture**

Control/operation element	Rotative
---------------------------	----------

**Materials**

Colour	Polar white
RAL code	9010
Surface finish	Glossy
Material	Thermoplastic
Treatment	Untreated

**Dimensions**

Height	58.30 mm
Width	58.30 mm
Depth	18.90 mm
Diameter axis	4 mm

**Connectivity**

Mounting type	Screw mounting
---------------	----------------

**Equipment**

Monitoring window/light outlet	No
--------------------------------	----

**Accessories**

Has labelling field	No
---------------------	----

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Texts**

Imprint	With imprinted symbol curve
Installation mode	For screw fastening

**Suitable for**

R.x	
-----	--

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes