

Product Datasheet

VF418PY



VF418PY

Small distributor,golf,flush,4row,72M,QC-terminal,N+PE,white door

Technical Features

Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Flush mounting

Electric current

Rated current	63 A
---------------	------

Equipment

Number of rails	4
Number of rows	4
Number of section in width	1
With lock	No
Has neutral terminal block	Yes

Capacity

Number of modules	72
-------------------	----

Functions

With conduit inlets	Yes
---------------------	-----

Dimensions

Height	688 mm
Width	460 mm
Depth	97.50 mm
Built-in height	652 mm
Built-in width	426 mm

Cover, door

Number of cabinet doors	1
-------------------------	---

Dimensions

Built-in depth	72 mm
----------------	-------

Cover, door

Number of locks	0
-----------------	---

Dimensions

Number of width units	18
-----------------------	----

Cover, door

Door/cover is transparent	No
---------------------------	----

Materials

Material	Plastic
RAL code	9010
Colour	Pure white

Equipment

Has earthing terminal block	Yes
Has mounting plate	No

Materials

Ultraviolet-resistant	No
-----------------------	----

Safety

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP40

Product Datasheet

VF418PY

Safety

Locking type	Snap on lock
	Without lock
Glow wire test	850 °C

Sustainability

RoHS conform	Yes
--------------	-----