



HXA024H

**Alarm contact 1NO+1NC 250V AC (x160-P160-x250-P250-x630-P630)**

**Technical Features**

**Electric current**

Rated current	3 A
Rated current 230 V AC15	3 A

**Connectivity**

Type of connection	quickconnect
Mounting type	Click mounting

**Connection**

Type of contacts	1NC+1NO
Cross-section flexible conductor	0.5 - 1.25 mm <sup>2</sup>
Cross-section rigid conductor	0.5 - 1.25 mm <sup>2</sup>

**Voltage**

Rated insulation voltage U <sub>i</sub>	250 V
Rated impulse withstand voltage U <sub>imp</sub>	1500 V
Type voltage supply	AC/DC

**Power**

Total power loss under I <sub>N</sub>	3 W
---------------------------------------	-----

**Equipment**

Number of INV contacts	0
Number of NC contacts	1

**Safety**

Ingress Protection (IP) class	IP4X
-------------------------------	------

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes