



WPPS22

## 10AX 2 Gang 2 Way Wall Switch & Back Box with Knockouts

### Technical Features

#### Electric current

Switching current	10 A
-------------------	------

#### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

#### Voltage

Rated voltage	250 V
---------------	-------

#### Materials

Colour	Grey
Surface finish	Glossy
Material	Steel
Treatment	Epoxy

#### Identification

Assembly arrangement	Basic element with complete housing
----------------------	-------------------------------------

#### Connectivity

Mounting type	Screw mounting
---------------	----------------

#### Controls and indicators

Number of buttons	2
-------------------	---

#### Dimensions

Dimensions	86 x 86 mm
Built-in depth	0 mm

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Architecture

Control/operation element	Double rocker
---------------------------	---------------

#### Electric current

Rated current	10 A
---------------	------

#### Texts

Installation mode	For flush-mounted and hollow wall mounting
Lighting	With control LED for ON
Switch mode	2-way

#### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes