Product Datasheet
VF418TF

VF418TF3

Small distributor,golf,flush,4row,IP40,72M,MS-terminal,PE,transparent door

Technical Features

Voltage	
Nominal voltage	400 - 400 V
Installation, mounting	
Suitable for outdoor usage	No
Mounting on	Flush mounting
Electric current	
Rated current	63 A
Equipment	
Number of rails	4
Number of rows	4
Number of section in width	1
With lock	No
Has neutral terminal block	No
Capacity	
Number of modules	72
Functions	
With conduit inlets	Yes
Dimensions	
Height	688 mm
Width	460 mm
Depth	97.50 mm
Built-in height	652 mm
Built-in width	426 mm
Cover, door	
Number of cabinet doors	1
Dimensions	
Built-in depth	72 mm
Cover, door	
Number of locks	0
Dimensions	
Number of width units	18
Cover, door	
Door/cover is transparent	Yes
Materials	
Material	Plastic
RAL code	9010
Colour	Pure white
Equipment	
Has earthing terminal block	Yes
Has mounting plate	No
Materials	
Ultraviolet-resistant	No
Safety	
Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP40

Safety	
Locking type	Snap on lock Without lock
Glow wire test	650 °C

Sustainability	
RoHS conform	Yes