



WGDL111NP-12VKB

## 12V 1G press switch with led;kb

### Technical Features

#### Electric current

|                   |      |
|-------------------|------|
| Switching current | 10 A |
|-------------------|------|

#### Voltage

|               |       |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

#### Frequency

|           |          |
|-----------|----------|
| Frequency | 50-60 Hz |
|-----------|----------|

#### Architecture

|                           |               |
|---------------------------|---------------|
| Control/operation element | Single rocker |
| Number of poles           | 1             |

#### Power

|                                  |     |
|----------------------------------|-----|
| Fluorescent lamps in duo circuit | 0 W |
|----------------------------------|-----|

#### Materials

|                |                    |
|----------------|--------------------|
| Colour         | Knight black       |
| Surface finish | Matt               |
| Material       | Polycarbonate (PC) |
| Treatment      | Varnished          |
| Transparent    | No                 |

#### Dimensions

|                |       |
|----------------|-------|
| Height         | 22 mm |
| Width          | 90 mm |
| Depth          | 25 mm |
| Built-in depth | 25 mm |

#### Installation, mounting

|             |               |
|-------------|---------------|
| Mounting on | Wall mounting |
|-------------|---------------|

#### Controls and indicators

|                   |   |
|-------------------|---|
| Number of buttons | 1 |
|-------------------|---|

#### Connectivity

|                    |                |
|--------------------|----------------|
| Type of connection | Screw terminal |
|--------------------|----------------|

#### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
| Impact resistance IK          | IK02 |

#### Accessories

|                     |    |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

#### Texts

|             |       |
|-------------|-------|
| Switch mode | 1-way |
|-------------|-------|

#### Suitable for

|       |  |
|-------|--|
| shark |  |
|-------|--|

#### Sustainability

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|