

# Product Datasheet

## TYA720



TYA720



### Time switch yearly cycle 4 channels KNX

#### Technical Features

##### Settings

|                              |     |
|------------------------------|-----|
| Supported configuration mode | ETS |
|------------------------------|-----|

##### Voltage

|                            |           |
|----------------------------|-----------|
| Operating voltage over bus | 21 - 32 V |
|----------------------------|-----------|

##### Connectivity

|                           |    |
|---------------------------|----|
| With bus system KNX radio | No |
|---------------------------|----|

##### Equipment

|                    |   |
|--------------------|---|
| Number of channels | 4 |
|--------------------|---|

##### Scope of delivery

|                         |     |
|-------------------------|-----|
| Bus connection included | Yes |
|-------------------------|-----|

##### Functions

|                        |     |
|------------------------|-----|
| Power reserve in years | 5 y |
|------------------------|-----|

##### Use conditions

|                       |             |
|-----------------------|-------------|
| Operating temperature | -10 - 50 °C |
|-----------------------|-------------|

##### Materials

|        |            |
|--------|------------|
| Colour | Light grey |
|--------|------------|

##### Texts

|          |                     |
|----------|---------------------|
| Function | Presence simulation |
|----------|---------------------|

##### Capacity

|                   |   |
|-------------------|---|
| Number of modules | 4 |
|-------------------|---|

##### Sustainability

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |