



EZN003



**Adjustable time on timer**

**Technical Features**

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Power**

Power consumption during operation	15 VA
Power loss at full load	2 W
230 V incandescent and halogen lamp	450 W

**Use conditions**

Operating temperature	-20 - 50 °C
Storage/transport temperature	-40 - 70 °C

**Connection**

Cross-section flexible conductor	1 - 6 mm <sup>2</sup>
Cross-section rigid conductor	1.5 - 10 mm <sup>2</sup>
Number of contacts	1
Type of contacts	1x changeover

**Capacity**

Number of modules	1
-------------------	---

**Texts**

Switch mode	Change-over contact, usable as NC or NO
Function	Functions: On delay, off delay, single shot leading edge/single shot trailing edge, pulse shaping, flashing symmetrically, contact open/closed
Type of connection	With screw terminals
Installation mode	For mounting on DIN rail

**Dimensions**

Height	85 mm
Width	17.50 mm
Depth	58 mm

**Electric current**

Acceptable current rating AC1	8 A
-------------------------------	-----

**Equipment**

Number of NC contacts	0
Number of NO contacts	0
Switch off delay	Yes
Switch on delay	Yes

**Settings**

Time delay	0.1 S - 10 h
------------	--------------

**Voltage**

Type voltage supply	AC/DC
---------------------	-------

Illustrations | Drawings

