



UDKPQ06E

floor box set cpl. incl. st. steel cassette Q06, outlet box sq, socket outlets

Technical Features

Architecture

With carpet protection frame	No
With opening carpeting	Yes

Dimensions

Built-in depth	105 mm
Built-in width	200 mm
Built-in length	200 mm
Length	217 mm
Width	200 mm
Thickness of carpet recess	23 mm

Configuration

Installation size (underfloor installations)	Q06
--	-----

Installation, mounting

Suitable for recessed floor mounting	Yes
Suitable for concrete installation	Yes
Suitable for outdoor usage	No
Suitable for raised floor installation	Yes
Suitable for wet cleaning	No

Instructions

Floor maintenance	Dry
-------------------	-----

Materials

Material	Stainless steel
----------	-----------------

Use conditions

Vertical load applied across large surface area (heavy load)	3 kN
Vertical load applied across small surface area	1.5 kN

Functions

Suitable for sub-floor duct	Yes
-----------------------------	-----

Shape

Shape	Square
-------	--------

Texts

Cable outlet	With cable outlet in cover
--------------	----------------------------

Materials

Colour	Stainless steel
--------	-----------------

Connection

Number of conduit inlets	1
Number of sockets SCHUKO	6

Equipment

Number of built-in devices	6
Number of outlet boxes	2

Safety

Ingress Protection (IP) class	IP20
Protection class in unused condition	IP30

Illustrations | Drawings

