



503404



Group push-button, 4NO contacts, comm. input terminal, neut. pos., light control

Technical Features

Electric current

| | |
|---------------------------|------|
| Switching current | 10 A |
| Momentary contact current | 10 A |

Voltage

| | |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

Architecture

| | |
|---------------------------|---------------|
| Control/operation element | Double rocker |
| Number of poles | 0 |

Materials

| | |
|----------------|------------------|
| Surface finish | Matt |
| Material | Metal Plastic |
| Treatment | Untreated |
| Transparent | No |

Dimensions

| | |
|------------------------------------|----------|
| Height | 71 mm |
| Width | 71 mm |
| Depth | 41.60 mm |
| Built-in depth flush-mounted boxes | 35 mm |

Installation, mounting

| | |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

Controls and indicators

| | |
|------------------------------|-------------------|
| Number of buttons | 2 |
| Type of push button | Group push button |
| With feedback signal contact | No |

Connectivity

| | |
|--------------------|----------------|
| Type of connection | Screw terminal |
|--------------------|----------------|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
| Impact resistance IK | IK07 |

Accessories

| | |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

Texts

| | |
|--------------------|-----------------------|
| Imprint | Without imprint |
| Installation mode | With spreader claws |
| Lighting | For illumination |
| Switch mode | With neutral position |
| Type of connection | With screw terminals |

Suitable for

K.x / Q.x / R.x / S.x/B.x

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|