



VZ032D

Pressure balance screw joint, vector, IP66, M32

Technical Features

Dimensions

Spanner width in mm	41 mm
Thread length	9 mm

Connection

Clamping range	13 - 21 mm
----------------	------------

Materials

Material	Plastic Thermoplastic
Colour	Light grey
RAL code	7035
Treatment	Untreated

Safety

Impact-resistant	Yes
Ingress Protection (IP) class	IP65

Use conditions

Operating temperature	-25 - 40 °C
-----------------------	-------------

Equipment

Thread size metric	0 - 32
With bending protection	Yes
With locknut	Yes
Safe use in explosive atmosphere	No
Thread pitch	1.50

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes