



VZ032M

Cable gland, vector, IP65, M32, plastic

Technical Features

Dimensions

| | |
|---------------------|-------|
| Height | 50 mm |
| Spanner width in mm | 36 mm |
| Thread length | 10 mm |

Connection

| | |
|----------------|------------|
| Clamping range | 15 - 21 mm |
|----------------|------------|

Materials

| | |
|-----------|---------------------------------|
| Material | Polyamide (PA) Thermoplastic |
| Colour | Light grey |
| RAL code | 7035 |
| Treatment | Untreated |

Safety

| | |
|-------------------------------|------|
| Impact-resistant | Yes |
| Ingress Protection (IP) class | IP65 |

Use conditions

| | |
|-----------------------|--------------|
| Operating temperature | -20 - 100 °C |
|-----------------------|--------------|

Equipment

| | |
|----------------------------------|--------|
| Thread size metric | 0 - 32 |
| With bending protection | Yes |
| With locknut | Yes |
| Safe use in explosive atmosphere | No |
| Thread pitch | 1.50 |

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |