



HXA021H

**Auxiliary contact 1NO+1NC 250V AC (x160-P160-x250-P250-x630-P630)**

**Technical Features**

**Electric current**

Rated current 230 V AC15	3 A
--------------------------	-----

**Connectivity**

Type of connection	quickconnect
Mounting type	Click mounting

**Connection**

Type of contacts	1NC+1NO
------------------	---------

**Voltage**

Rated insulation voltage $U_i$	250 V
Rated impulse withstand voltage $U_{imp}$	1500 V
Type voltage supply	AC/DC

**Power**

Total power loss under IN	3 W
---------------------------	-----

**Equipment**

Number of INV contacts	0
Number of NC contacts	1

**Safety**

Ingress Protection (IP) class	IP4X
-------------------------------	------

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes