



VD118PT

Sm.distr.,VD/IC²,surface,1row,18M,IP40,MS-terminals,AUS,N+PE,white door

Technical Features

Voltage

Nominal voltage 400 - 400 V

Installation, mounting

Suitable for outdoor usage No

Mounting on Surface mounting

Electric current

Rated current 63 A

Equipment

Number of rails 1

Number of rows 1

Number of section in width 1

With lock No

Has neutral terminal block Yes

Capacity

Number of modules 18

Functions

With conduit inlets Yes

Dimensions

Height 200 mm

Width 400 mm

Depth 91 mm

Cover, door

Number of cabinet doors 1

Number of locks 0

Dimensions

Number of width units 18

Cover, door

Door/cover is transparent No

Materials

Material Plastic

RAL code 9010

Colour Pure white

Equipment

Has earthing terminal block Yes

Has mounting plate No

Materials

Ultraviolet-resistant No

Safety

Protection class Isolation class II

Ingress Protection (IP) class IP40

Locking type Snap on lock
Without lock

Glow wire test 650 °C

Sustainability

RoHS conform Yes