

Product Datasheet

BFC480E



BFC480E

Earth leakage add-on-block 4P 125A 300mA type AC

Technical Features

Electric current	
Rated current	125 A
Rated residual operating current I _{dn}	300 mA

Architecture	
Number of poles	4

Safety	
Residual current type	AC

Voltage	
Rated insulation voltage U _i	500 V
Rated impulse withstand voltage U _{imp}	6000 V

Connection	
Cross-section of input and output with screws, for massive conductors	10 - 70 mm ²
Cross-section of input and output with screws, for flexible conductors	10 - 50 mm ²

Connectivity	
Type of connection	Screw terminal
Down connection alignment for modular devices	Aligned terminal

Dimensions	
Height	103 mm
Width	213 mm
Depth	69 mm

Sustainability	
RoHS conform	Yes

Illustrations | Drawings

