




75642134



KNX glass sensor 2g thermostat, display, intg bus coupl , KNX-TS sensor, al.

Technical Features

Installation, mounting

Mounting on Flush mounting

Use conditions

Operating temperature -5 - 45 °C

Functions

With room temperature controller Yes

Power

Current consumption 23 mA

Dimensions

Built-in depth	24.20 mm
Built-in depth flush-mounted boxes	27 mm
Height	160 mm
Width	86 mm
Depth	37.70 mm

Equipment

Number of actuation points 6

Controls and indicators

With LED indication Yes

Materials

Colour	Aluminium
RAL code	9006
Material	Aluminium Glass
Surface finish	Glossy

Accessories

Has labelling field No

Screen

With display Yes

Texts

Function	For switch, push-button, dimmer, blind and thermostat functions With valve protection function
Installation mode	For vertical mounting
Operating mode	Controller operating modes: comfort, standby, night and frost/heat protection mode
Temperature	Additional connection for external temperature sensor Temperature measurement via internal Temperature sensor or external communication object
Voltage	Operation with non-choked output of KNX voltage supply possible (pay attention to current consumption) Separate auxiliary power supply needed

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes