



503101



Push-button NO contact with two signal contacts

Technical Features

Electric current	
Switching current	10 A
Momentary contact current	10 A

Voltage	
Rated voltage	250 V

Architecture	
Control/operation element	Rocker

Materials	
Material	Metal Plastic
Transparent	No

Dimensions	
Height	71 mm
Width	71 mm
Depth	41.60 mm
Built-in depth	31 mm
Built-in depth flush-mounted boxes	35 mm

Installation, mounting	
Mounting on	Flush mounting

Controls and indicators	
Number of buttons	1
Type of push button	Single push button
With feedback signal contact	Yes

Safety	
Ingress Protection (IP) class	IP20
Impact resistance IK	IK07

Texts	
Imprint	Without imprint
Installation mode	With spreader claws
Lighting	For lighting and monitoring circuit
Switch mode	NO, with 2 separate signalling contacts
Type of connection	With plug-in terminals

Suitable for	
K.x / Q.x / R.x / S.x/B.x	

Sustainability	
Halogen free	Yes
RoHS conform	Yes